

Inovo All-Brass Regulator

HCPCS:

- Up to two optional PTO outlets with check valves
- 12-position flow dial (0.25, 0.50, 1.0, 2.0, 3.0, 4.0, 6.0, 8.0, 10.0, 15.0, 25.0 LPM) (excluding IN2800-R-2, 1 Flow setting, 100 LPM)
- Meets ASTM-G175-13 promoted ignition tests
- Inlet pressure: 500 - 3,000 psi
- Outlet pressure: 50 ps
- Outlet type: Barb
- 5 years expected service live
- 2-year limited warranty
- Assembled and tested in the USA
- UL-listed, impact resistant gauge

PRODUCTS	Description
IN2800-R-2	AllBrass,CGA540,Barb,2 PTO,1/EA
IN2925-R	AllBrass,0-25LPM,CGA870,Barb,0 PTO,1/EA
IN2925-R-1	AllBrass,0-25LPM,CGA870,Barb,1 PTO,1/EA
IN2925-R-2	AllBrass,0-25LPM,CGA870,Barb,2 PTO,1/EA

SPECIFICATIONS	Description
Warranty	2-year limited warranty
Color	Silver & Red
Liter Flow	IN2800-R-2: 1 setting (100 LPM) IN2925-R, IN2925-R-1 and IN2925-R-2: 12 settings (0.25, 0.5, 1.0, 2.0, 3.0, 4.0, 6.0, 8.0, 10.0, 15.0, 25.0 LPM)
Product Type	Oxygen Regulator

PARTS	Description
SEAL100	Seal Washer,Conservers/Regulators,10/pkg, PKG