

Drive DeVilbiss 10L Oxygen Concentrator

HCPCS: E1390



FIGURE A



FIGURE B

- Built upon the reliable features of the 525 concentrator, the 1025 Oxygen Concentrator is designed to provide optimal oxygen delivery for patients with varying flow requirements
- Assembled in the USA and built in the same shell as the 5 Liter, the 10 Liter Concentrator is also compatible with cylinder transfill systems
- Sold separately, the Transfill Caddy is designed with a steel frame to simply connect the 18 x 14 inch shelf, designed to support up to 40 lbs., to the DeVilbiss 10L Concentrator
- Front view (Figure A), Rear View (Figure B)
- With a weight of 42 lbs. and an identical footprint to the 525 unit, the 1025 is substantially smaller and lighter than competitive 10 Liter concentrators
- Capable of delivering 87% to 96% of O purity from 2 to 10 LPM, the 10 Liter Concentrator is an ideal investment for your patients and business alike
- Exclusive DeVilbiss OSD® (Oxygen Sensing Device), standard on every unit, monitors the oxygen produced and ensures patient safety and reliability for longer service intervals
- Equipped with accessible patient controls, bright LEDs that can be seen from a distance, protected cannula fitting and recessed humidifier nook to prevent damage

PRODUCTS

Description

1025DS	10L Compact Concentrator, 110v, 1/ea
--------	--------------------------------------

SPECIFICATIONS

Description

Delivery Rate	2.0 to 10.0 LPM
Outlet Pressure	20.0 PSI ± 1.0 PSI
Oxygen Percentage	2-10 LPM, 87-96%
Power Consumption	120VAC, 60Hz
Power Input	639W (avg)
Product Length	24.5"
Product Overall Height (FW17 FW19)	12"
Product Weight 2 4 6	42 lbs.
Warranty Limited	3 Years

ACCESSORIES

Description

303DZ-605	AIR FILTER 6-PKG - DFT, PK
1025D-605	INTAKE FILTER SSP, 1/ea, EA
1025D-682	COMPRESSOR FILTER SSP, 1/ea, EA
PV5LD-651	FINAL BACTERIA FILTER - DFT, 1/EA, EA
525DD-650	Transfill Rack System, 525DS Series, 1ea, EA

ACCESSORIES**Description**

PF1100TUB	Transfill Connection Tubing, 1/ea, EA
XM-1	DISS Adapter plastic,25/Bag, EA
1025D-685	Adapter for Humidifier Bottle, EA
HUM 001	Humidifier Bottle PI 50/CS, CS

PARTS**Description**

1025D-603	DOMESTIC BASE PKG, EA
525DD-636	Plastite Screw SS Pkg, EA
1025DS-616	CAPACITOR, DS SSP, 1/ea, EA
1025D-615	COMPRESSOR BOX SSP, EA
1025D-632	COMPRESSOR PLATE SSP, EA
1025D-643	DS COMPRESSOR REBUILD KIT SSP, 1/ea, EA
505DZ-634	SILICON TUBING (2'), EA
525DD-639	DOOR INTAKE FILTER PACKAGE, EA
1025D-607	FLOW METER 10L SSP, EA
525DD-611	Front Cover Package, 1/ea, EA
1025D-655	FORMED METAL TUBE SSP, EA
1025D-623	WIRE HARNESS ASSEMBLY, DS SSP, 1/ea, EA
1025D-609	MOTOR MONT SSP, EA
525DD-606	Concentrator (5L, 10L) Outlet Port, 1/ea, EA
1025D-622	PC BOARD ASSEMBLY SSP, EA
1025D-612	PRESSURE REGULATOR, EA
MC29D-612	PRESSURE REGULATOR ASSY, EA
1025D-617	PURGE HARNESSE ASSEMBLY, EA
525DD-612	Rear Cover Package - No Aux Port, 1/ea, EA
515ADZ-702	ROTARY VALVE REPLACEMENT, EA