

Dual Channel TENS

HCPCS: E0730



- Dual isolated channels
- Pulse amplitude adjustable from 0-80 mA, 500 ohm load
- Pulse frequency adjustable from 2-150 Hz
- Pulse width is adjustable from 30-260 micro-seconds
- Wave form: asymmetrical, bi-phase, square pulse
- Modulation selector offers wave delivery in Normal, Burst or Modulation modes
- Plastic belt clip
- Comes complete with carrying case, 2 lead wires, 9-volt battery, 1 package of 4 pre-gelled electrodes and operating manual

PRODUCTS

Description

AGF-602	TENS Dual Channel w/Timer 1/bx
---------	--------------------------------

SPECIFICATIONS

Description

Warranty	3 Year Limited
----------	----------------