

## Delta Ultra-Light 1000 Full-Electric Low Bed

HCPCS: E0266



FIGURE A



FIGURE B




FIGURE C



FIGURE D



FIGURE E



FIGURE F

- The Delta 1000 is truly universal because the bed frame can be used with Drive's and most other manufacturers bed ends, old and new
- The transition box mounted on the foot section is key to interchangeability (Figure A)
- The transition box allows you to change the rotation of the high/low shaft
- Headboard is taller than footboard to better fit home decor (Figure B)
- The wood grain panels are break and scratch resistant
- Once installed, the high/low shaft will stay with the bed to eliminate loss or forgetting on future installations (Figure C)
- Labels and color-coded springs assure accurate installation of side rails for patient safety (Figure D)
- Unique motor is completely self-contained to reduce weight and noise
- 9 ½" to 23 ½" deck height
- Easy to set up
- Top mounted Hi/Lo crank accessibility
- Height-adjustable motor comes pre-installed on the foot section
- Caster easily moves from standard to low bed position
- The motor assembly can be installed and removed with patient in bed
- Bed, side rails and mattress safety-tested by SGS, a nationally recognized testing facility Satisfies all applicable FDA entrapment guidelines
- The motor is UL approved
- In the event of a power failure, a 9 volt battery, located in the hand control, can lower the head and foot sections nine times
- New and improved hand pendant has large, easy-to-use controls (Figure E)
- Bed ships in two cartons
- Hand crank located on the top of the footboard prevents bending for the caregiver when in the low position (Figure F)
- Channel frame construction provides superior strength and reduced weight
- Zinc-coated spring deck
- Extension kit available (model #15030EXTKIT) extends length from 80" to 84"
- Patent Pending
- Weight Capacity 450 lbs

### PRODUCTS

### Description

| PRODUCTS        | Description                                      |
|-----------------|--|
| 15235           | Delta Ultra-Light 1000 Full-Electric Low Bed, CS |
| 15235BV-FR      | Delta Ultra-Light 1000 Full-Electric Low Bed, CS |
| 15235BV-HR      | Delta Ultra-Light 1000 Full-Electric Low Bed, CS |
| 15235BV-PKG     | Delta Ultra-Light 1000 Full-Electric Low Bed, CS |
| 15235BV-PKG-1   | Delta Ultra-Light 1000 Full-Electric Low Bed, CS |
| 15235BV-PKG-1-T | Delta Ultra-Light 1000 Full-Electric Low Bed, CS |
| 15235BV-PKG-2   | Delta Ultra-Light 1000 Full-Electric Low Bed, CS |
| 15235BV-PKG-T   | Delta Ultra-Light 1000 Full-Electric Low Bed, CS |

| SPECIFICATIONS                     | Description   |
|------------------------------------|---|
| Bed Height Maximum With Casters    | 23.5"   |
| Bed Height Minimum Without Casters | 9.5"  |
| Carton Shipping Weight             | 191 lbs.  |
| Unit Dimensions                    | 36" (W) x 88" (L)   |
| Warranty                           | (Original Purchaser) 5 Years on Motor and Hand Control, Limited Lifetime on Welds and Frame, 1 Year on All Other Parts and Components |
| Weight                             | 175 lbs.  |
| Weight Capacity                    | 450 lbs   |
| Bed Height Min wo caster           | 9.5"  |
| Bed Height Max w casters           | 23.5"   |
| ACCESSORIES                        | Description   |
| 15030HBL                           | Hospital Bed Linen Kit,1 EA,10/CS, CS   |
| 15030HBC                           | Bedding in a Box,1 EA,5/CS, CS  |
| PARTS                              | Description   |
| 15044CSET                          | Set of 4 Casters,Homecare Bed, 1 set ea, CS   |
| 15235                              | LowBed,UltraLightFull.Elec.1/c, CS  |
| 15547F-FP-1                        | Foot Board Panel, 15235, Delta Bed, 1/ea, CS  |
| 15547H-HP-1                        | HeadBoardPanel,15235/15547H,DeltaBed,1ea, CS  |
| 15044CL                            | Caster,w/Lockfor15544,15547,1/ea, CS  |
| 15044CNL                           | Caster,NoLockfor15544,15547,1/ea, CS  |
| 15541                              | Head Spring,15030/15033,Delta Bed,1ea, CS   |
| 15030-FRLINK                       | FrameLinkw/DeckScrews,15030,15005,1/ea, CS  |
| 15544HGB                           | Head Board Gear Box,15544,1ea, CS   |
| 15544FGB                           | Foot Board Gear Box,15544,1ea, CS   |
| 1503C                              | Locking Collar Universal Bed Shaft,1ea, CS  |
| 15544GBMB                          | MountingBracketForTransBox15030,1ea, CS   |
| 15033MHLNC-N                       | HiLoMotorConnector15033MHLN-MGBA,1ea, CS  |
| 15030UBS                           | Delta Bed Shaft,1ea, CS   |
| 15030MC                            | Cap Only for 15030 Motor,1/ea, CS   |
| 15030-MS                           | Motor Strap,Ultra Lite Bed,2 per PKG, CS  |
| 15030PN-1035                       | HeadActuatorBarDeltaFlatTubing,1ea, CS  |
| 15030PN-1036                       | FootActuatorBarDeltaFlatTubing,1ea, CS  |
| 15030-7RMM                         | Motor Mount,7 R Serial,1/ea, CS   |
| 15030P-1006                        | Covers,UltraLt.Bed Okin,1/bx, CS  |