

Delta® Ultra- Light 1000, Semi-Electric Bed

HCPCS:



FIGURE A



FIGURE B



FIGURE C



FIGURE D



FIGURE E

- The Delta 1000 is truly universal because the bed frame can be used with Drive's and most other manufacturers bed ends, old and new
- The transition box mounted on the foot section is key to interchangeability (Figure A)
- The transition box allows you to change the rotation of the high/low shaft
- Headboard is taller than footboard to better fit home decor (Figure B)
- The wood grain panels are break and scratch resistant
- Foot section weighs 50% less than conventional foot sections to make deliveries safe and easy
- Once installed, the high/low shaft will stay with the bed to eliminate loss or forgetting on future installations (Figure C)
- Labels and color-coded springs assure accurate installation of side rails for patient safety (Figure D)
- Unique motor is completely self-contained to reduce weight and noise
- The motor assembly can be installed and removed with patient in bed
- Bed, side rails and mattress safety-tested by SGS, a nationally recognized testing facility
- Satisfies all applicable FDA entrapment guidelines
- The motor is UL approved
- In the event of a power failure, a 9 volt battery, located in the motor, can lower the head and foot sections nine times
- No crank needed
- New and improved hand pendant has large, easy-to-use controls (Figure E)
- Bed ships in two cartons
- Channel frame construction provides superior strength and reduced weight
- Zinc-coated spring deck
- Extension kit available (model #15030EXTKIT) extends length from 80" to 84"
- Patent Pending
- Weight Capacity 450 lbs

PRODUCTS

Description

PRODUCTS	Description
15030	SemiElectricUltraLtBed,1/cs
15030BV-FR	UltraLt.PlusSemiElecBedw/FullR
15030BV-HR	UltraLt. PlusSemiElecBedw/Half
15030BV-PKG	UltraLt.PlusSemi.Elec.BedPkg,1
15030BV-PKG-1	Ultra Lt.Semi-ElecBed Pkgw/Half
15030BV-PKG-11	Delta Semi,FullRail,QuickEasyFoam,1ea
15030BV-PKG-12	Delta Semi,HalfRail,QuickEasyFoam,1ea
15030BV-PKG-1-T	Ultra Lt.Semi-ElecBed Pkgw/Half
15030BV-PKG-2	Ultra Lt.PlusSemiElecBedPkg,1 p
15030BV-PKG-4	Semi Electric Ultra Lt.Bed Pkg,1/cs
15030BV-PKG-T	UltraLt.PlusSemi.Elec.BedPkg,1

SPECIFICATIONS	Description
Carton Shipping Weight	179 lbs.
Unit Dimensions	36" (W) x 88" (L) Overall Sleep Surface 36" W x 80" L
Warranty	(Original Purchaser) 5 Years on Motor and Hand Control, Limited Lifetime on Welds and Frame, 1 Year on All Other Parts and Components
Weight	163 lbs.
Weight Capacity	450 lbs
ACCESSORIES	Description
15030HBC	Bedding in a Box,1 EA,5/CS, CS
15030HBL	Hospital Bed Linen Kit,1 EA,10/CS, CS
PARTS	Description
15544HP-1	Head Board Panel, 15544H, 1/ea, EA
15544F-CH	Foot Board Crank Holder, 1/ea, EA
15044CNL	Caster,NoLockfor15544,15547,1/ea, EA
15044CL	Caster,w/Lockfor15544,15547,1/ea, EA
15005P-1040	Hooks to Attch Sleep Surface,6/bx, BX
15030MC	Cap Only for 15030 Motor,1/ea, EA
15030P-1006	Covers,UltraLt.Bed Okin,1/bx, BX
15030-MS	Motor Strap,Ultra Lite Bed,2 per PKG, PKG
15030-7RMM	Motor Mount,7 R Serial,1/ea, EA
15030PN-1036	FootActuatorBarDeltaFlatTubing,1ea, EA
15030PN-1035	HeadActuatorBarDeltaFlatTubing,1ea, EA
1503C	Locking Collar Universal Bed Shaft,1ea, EA
15030HC-G	Hand Control for 15030MO 15038MO,1/ea, EA
15544GBMB	MountingBracketForTransBox15030,1ea, EA
15544C	Hand Crank,Ultra Lite Bed,1ea, EA
15544GBD	Transition Dual Gear Box,15544,1ea, EA
15038MO	Motor 15038 W/Fuse, 1/ea, EA
15541	Head Spring,15030/15033,Delta Bed,1ea, EA
15030-FRLINK	FrameLinkw/DeckBolts,15030,15005, 1/ea, EA
15548	Foot Spring,15030,Delta Bed,1ea, EA