

Prime Care Bed Model P703



HCPCS:



FIGURE A




FIGURE B



FIGURE C



FIGURE D



FIGURE E

- 550 lbs. weight capacity, Resident Weight 500 lbs
- 7" to 30" height range
- Optional integrated width adjusts to 39" - 42" (Figure A)
- Integrated 76", 80" and 84" sleep surface length (Figure B)
- Two way Red/Green color coded floor lock system (Figure C)
- Eight (8) Function Handheld Pendant Control
- Auto Contour
- 4 DC Motors Synchronized Hi/Lo control system keeps bed level
- Four sealed bearings secured in "G" track
- IV pole holders
- Extended Heel Lift
- Eight 3" Heavy Duty casters roll at any height
- Fixed adjustable wall bumper (Figure D)
- Options:
 - > Staff Control with Trend/Reverse Trend and Cardiac Chair (Figure E)
 - > 88" length Extension (Figure F)
 - > Deluxe Assist Rails, Assist Bars
 - > Bed ends, two styles and three wood grain laminate colors
 - > Battery Back-up, Bed Transporter, Trapeze - Battery Back-up (P703-BBK), Bed Transporter (P903TRP)

PRODUCTS	Description
P703	Prime Care Model P703, 1 ea

SPECIFICATIONS	Description
Bed Height Range	7" - 30"
Bed Length Range	76", 80" or 84"
Bed Width	36"
Unit Dimensions	38.5" (w) x 85.25" (L) x 8" (H)
Warranty	Lifetime on Welds; 15 Year on Frame; 5 years on Electrical
Weight	205 lbs.
Weight Capacity	Accommodate up to 550 lbs. Maximum Resident Weight 500 lbs.

ACCESSORIES	Description
PLTCDR	LTC Deluxe Rail, 1PR, PR
PLTCAR	LTC Assist Rail, 1PR, PR
PLTCAB	LTC Assist Bar, 1PR, PR
P703LE	P703 Length Extension 88", 1ea, EA

ACCESSORIES**Description**

P703-BBK	P703 Battery Backup,1ea, EA
P703SC04	Staff Control Panel f/P703 ,1ea, EA
P703WE	P703 Width Extension 39-42",1pr, PR
35BWBE-B-SC04	35" BRNWOOD BEW/SC04,OKOAK,EA, EA

PARTS**Description**

SP02-TH21060003	HandPendant,8-Button,703/1750/15904C, EA
SP02-PPB1750-3402E	Power Cord, 503/1750/15904C/200, 1/ea, EA
SP01-PCB900-24BS	BrakeStop,900/601/901/902/903/15902C/3, EA
SP01-UF16108061E	Hd/FtBrdBolt,P703/503,1ea, PKG
SP01-PCB300-01-57E	FtEdRchtAssy,900/01/02/03/TL500/703,1/PR, PR
SP01-TL500-29E	NonLckCastr,900/901/2/3/601/301/500/P200, EA