

## Deluxe Dual Channel TENS, Horizontal Design

HCPCS: E0730



- Horizontal design provides an improved ergonomic fit on belt
- New and improved lead wire connector will not disengage from TENS unit
- Easy and convenient "Flip Down" control panel and battery cover reduces cover loss or damage
- Dual isolated channels
- Adjustable 0-80 mA, 500 ohm load
- Pulse frequency adjustable 2-150 Hz
- Pulse width is adjustable from 60-250 micro-seconds
- Wave form: asymmetrical, bi-phase, square pulse
- Modulation selector offers wave delivery in Normal, Burst or Modulation modes
- Plastic belt clip
- Comes complete with carrying case, 2 lead wires with deluxe connector, 9-volt battery, 1 package of 4 pre-gelled electrodes and operating manual

**PRODUCTS**

**Description**

AGF-3X	Deluxe Dual Channel TENS, Horizontal Design, BX
--------	---

**SPECIFICATIONS**

**Description**

Warranty	3 Year Limited
----------	----------------