

## Digital Dual Channel 5 Mode TENS with Two Strength Duration Modes

HCPCS: E0730



- Digital wave technology provides a highly efficient delivery of the wave signal
- Dual isolated channels
- Intensity control is adjustable to 80 mA, 500 ohm load
- Pulse frequency adjustable from 0.5-150 Hz
- Pulse width is adjustable from 30-260 micro-seconds
- Wave form: asymmetrical, bi-phase, square pulse
- Modulation selector offers 5 modes of wave delivery, Normal, Burst and 3 Modulation modes
- Metal belt clip
- Comes complete with carrying case, 2 lead wires, 9-volt battery, 1 package of 4 pre-gelled electrodes and operating manual

### PRODUCTS

### Description

AGF-5X

Digital Dual Channel 5 Mode TENS with Two Strength Duration Modes, BX

### SPECIFICATIONS

### Description

Warranty

3 Year Limited