


## Drive Regulators

HCPCS:



- Drive regulators feature a protective contents gauge and a built-in pressure relief valve for safety
- Mini regulators offer the same function as standard regulators while facilitating an easier fit into oxygen carry bags
- Easy-to-operate single selector knob
- Lightweight and durable design
- Meet or exceed accuracy standards for ASTM, American National and CGA
- Inlet Pressure: 300 - 3,000 PSI
- Outlet pressure: 50 PSI
- UL Approved

PRODUCTS	Description
18300GN	Reg Ped, Gr, 0-4L, CGA870, Barb, 1/ea
18301G	Reg, Gr, 0-8L, CGA870, Barb, 1/ea
18301GM	Reg Mini, Gr, 0-8L, CGA870, Barb, 1/ea
18302GDEL	RegEng, Gr, 0-15L, CGA870, DISS, 1/ea
18302GMN	Reg Mini, Gr, 0-15L, CGA870, Barb, 1/ea
18302GN	Reg, Gr, 0-15L, CGA870, Barb, 1/ea
18303G	Reg, Gr, 0-8L, CGA540, DISS, 1/ea
18303GM	Reg Mini, Gr, 0-8L, CGA540, DISS, 1/ea
18304GMN	Reg Mini, Gr, 0-15L, CGA540, DISS, 1/ea
18304GN	Reg, Gr, 0-15L, CGA540, DISS, 1/ea
18307G	Reg Ped, Gr, 0-4L, CGA540, DISS, 1/ea

SPECIFICATIONS	Description
Warranty	Limited 3 Year

ACCESSORIES	Description
SEAL3000	Seal Washer, CHAD O2 Cnsrvrs&Regs,10/pkg, PKG
OM-900-FEC	E-Clip for Conserver Handles, 10/bag, BAG
SEAL100	Seal Washer,Conservers/Regulators,10/pkg, PKG