


Drive Regulators

HCPCS:



- Drive regulators feature a protective contents gauge and a built-in pressure relief valve for safety
- Mini regulators offer the same function as standard regulators while facilitating an easier fit into oxygen carry bags
- Easy-to-operate single selector knob
- Lightweight and durable design
- Meet or exceed accuracy standards for ASTM, American National and CGA
- Inlet Pressure: 300 - 3,000 PSI
- Outlet pressure: 50 PSI
- UL Approved

| PRODUCTS | Description |
|-----------|---|
| 18300GN | Reg Ped, Gr, 0-4L, CGA870, Barb, 1/ea |
| 18301G | Reg, Gr, 0-8L, CGA870, Barb, 1/ea |
| 18301GM | Reg Mini, Gr, 0-8L, CGA870, Barb, 1/ea |
| 18302GDEL | RegEng, Gr, 0-15L, CGA870, DISS, 1/ea |
| 18302GMN | Reg Mini, Gr, 0-15L, CGA870, Barb, 1/ea |
| 18302GN | Reg, Gr, 0-15L, CGA870, Barb, 1/ea |
| 18303G | Reg, Gr, 0-8L, CGA540, DISS, 1/ea |
| 18303GM | Reg Mini, Gr, 0-8L, CGA540, DISS, 1/ea |
| 18304GMN | Reg Mini, Gr, 0-15L, CGA540, DISS, 1/ea |
| 18304GN | Reg, Gr, 0-15L, CGA540, DISS, 1/ea |
| 18307G | Reg Ped, Gr, 0-4L, CGA540, DISS, 1/ea |

| SPECIFICATIONS | Description |
|----------------|----------------|
| Warranty | Limited 3 Year |

| ACCESSORIES | Description |
|-------------|--|
| SEAL3000 | Seal Washer, CHAD O2 Cnsrvrs&Regs,10/pkg, CS |
| OM-900-FEC | E-Clip for Conserver Handles, 10/bag, CS |