

DeVilbiss iFill® Personal Oxygen Station

HCPCS: K0738



FIGURE A



FIGURE B

- The DeVilbiss iFill Personal Oxygen Station offers a clinically focused and operationally efficient non-delivery oxygen solution a model that is great for patients and your business
- Makes it easy and convenient for your customers to fill portable oxygen cylinders in their homes and gives them greater freedom to come and go as they please
- Fills proprietary iFill cylinders - Standard 870 Post Valve or Integrated Continuous Flow regulator (Figure A-B)
- Easily tops off partially filled cylinders and automatically shuts off when filling is complete
- Control panel light signals when cylinder is filling and when its full
- Ergonomic design with easy-roll casters make iFill easy-to-move and store when not in use

| PRODUCTS | Description |
|----------------|----------------------------------|
| 535D | IFILL OXYGEN STATION |
| 535D-2C870 | IFILL PKG 2C W/870 POST VALVE |
| 535D-2CP | IFILL PKG 2 C W/OM-900, W/CASE |
| 535D-2D870 | IFILL PKG 2D W/870 POST VALVE |
| 535D-2DC | IFILL PKG 2 D W/CF REG |
| 535D-2DP | IFILL PKG 2 D W/OM-900, W/CASE |
| 535D-2E870 | IFILL PKG 2E W/870 POST VALVE |
| 535D-2EC | IFILL PKG 2 E W/CF REG |
| 535D-2EP | IFILL PKG 2 E W/OM-900, W/CART |
| 535D-2M6870 | IFILL PKG 2 M6 W/870 POST VALVE |
| 535D-M6-PD-PKG | IFILL PKG 2 M6, W/OM-900, W/CASE |

| SPECIFICATIONS | Description |
|-------------------------|------------------------------------|
| Cylinder Top Off | Yes |
| Electrical Requirements | 115V, 60 Hz, 4.1 Amps |
| Filling Time | 75 Minutes (M6 Cylinder) |
| Oxygen Purity | 93% +/- 3% |
| Power Consumption | 400 Watts Avg. |
| Product Dimensions | 28.5" (H) x 12.25" (W) x 22.5" (D) |
| Product Weight | 66 lbs |
| Sound Level | 50 dBA |
| Warranty | 3 Years or 3000 Hours |

| ACCESSORIES | Description |
|-------------|--|
| 535D-M6-870 | M6 CYL W/IFILL ADPT AND 870 POST VALVE, CS |
| 535D-C-870 | C CYL W/IFILL ADPT AND 870 POST VALVE, CS |

ACCESSORIES**Description**

| | |
|------------|--|
| 535D-D-870 | D CYL W/IFILL ADPT AND 870 POST VALVE, CS |
| 535D-D-CF | D CYLINDER W/CF REGULATOR, CS |
| 535D-E-870 | E CYL W/IFILL ADAPTOR AND 870 POST VALVE, CS |
| 535D-E-CF | E CYLINDER W/CF REGULATOR, CS |