

Drive Bonsai® Velocity Pneumatic Oxygen Conserver

HCPCS:



FIGURE A

- High-pressure oxygen only contacts brass; Low-pressure oxygen only contacts aluminum
- Delivers a uniform oxygen pulse at increments: 1, 2, 3, 4, 5 and 6
- Two continuous flow (CF) settings preset @ 2 LPM and 4 LPM
- Delivers up to a 6:1 savings ratio from 14 40 breaths per minute
- Operating pressure range: 500 3000 psi
- Light weight and quiet operation
- Easy-to-operate single selector knob
- Compact design: fits easily in virtually any oxygen carry bag

PRODUCTS	Description
OM-812	Bonsai Velocity Conserver, 25/cv
SPECIFICATIONS	Description
Warranty	Limited 2 Year
ACCESSORIES	Description
SEAL100	Seal Washer,Conservers/Regulators,10/pkg, PKG