

Vacu-Aide® Compact Suction Unit

HCPCS: E0600,A7001



FIGURE A



FIGURE B



FIGURE C

- The Vacu-Aide Compact is the smallest and strongest suction unit of its kind, while featuring a convenient carrying bag that provides discreet suction on the go (Figure A)
- Vacuum adjustment allows for 50-500 mm Hg +/- 10% and a free flow of 27 liters/minute (Figure B-C)
- Meets American Association for Respiratory Care (AARC) guidelines for neonatal, infant, child and adult homecare suctioning
- Enhanced battery life for up to one-hour operation
- Meets ISO10079-1:1999 high vacuum, high flow classification
- Travel-friendly design meets RTCA/DO-160E Aircraft Standard for Environmental Conditions and Test Procedures for Airborne Equipment (won't interfere with a planes navigation system)

PRODUCTS

Description

7310PR-D	Vacu-Aide Compact w/ Reusable Canister
----------	--

SPECIFICATIONS

Description

Battery Warranty	Limited 6 Months
Dimensions	7.25" (H) x 7.25" (W) x 6.75" (D)
Electrical Requirements	100-240 VAC, 50/60 Hz, 0.75 A max.; 12 V DC, 33 W max.
Flow Range	27 lpm free flow, unrestricted
Power Consumption	33 watts maximum
Vacuum Range	50-500 mm Hg
Waranty	Limited 2 Years
Weight	3.37 lbs with battery

ACCESSORIES

Description

7304D-619	BLACK 12V DC PWR COR, EA
7304D-636	VACUUM GAUGE TEST FIXTURE, EA
7310P-601	REPLACEMENT BATTERY, 1 EA., EA
7310P-602	REPLACEMENT BATT. DOOR,, EA
7310P-603	REUSABLE COLLECTION BOTTLE, EA
7310P-604	Reusable Collection Bottle. 6/pkg, PKG
7310P-606	CARRYING BAG, 7310PR SERIES, EA
7310P-615	COMPRESSOR SUBASSEMBLY, EA
7310P-616	MANIFOLD / REGULATOR, EA
7310P-617	CYLINDER / UMBRELLA VALVE, EA
7310P-618	REGULATOR KNOB SUBASSEMBLY, EA
7310P-619	KNOB LABEL, 7310, EA

ACCESSORIES**Description**

7310P-622	FRONT INSERT, 7310, EA
7310P-620	BOTTOM CAP, 7310, EA
7310P-623	REAR CASE HALF, 7310, EA
7310P-621	CASE HALF FRONT, 7310, EA
7310P-624	TOP CAP, 7310, EA
7310P-625	LABEL LED, DEVILBISS, EA
7310P-626	PC BOARD, EA
7310P-627	CASE SCREWS, EA

PARTS**Description**

6710D-609	AC POWER CORD, EA
099HD-614	LINE CORD PKG (dft), EA
9100D-603	BUMP-ON FEET KIT (PKG OF 4), EA